



EV9100-31

CB20-124E Water Filter

High flow big bowl housing



CB20-124E Housing: EV9100-31

BENEFITS

- High pressure housing includes head, mounting bracket and bowl
- Integral outlet pressure gauge monitors operation
- Complete modular package lets you expand capacity as needed

INSTALLATION TIPS

- Choose a mounting location which is suitable to support the full weight of the system when operating (30 lbs.)
- 3/4" FNPT inlet and outlet connection
- Install on cold water lines only
- Do not install where unit is exposed to direct sunlight
- Allow a minimum of 4" clearance under the filter to facilitate cartridge change
- Do not braze/solder fittings into head
- Never use a saddle valve for connection

OPERATION TIPS

- Change cartridge on a regular 6 month preventative maintenance program
- Change cartridge when the difference between the inlet pressure and the system outlet gauge is greater than or equal to 20 psi
- Service flow rate must not exceed 5.0 gpm
- Always flush the filter cartridge to drain for fifteen minutes at time of installation and cartridge change

APPLICATION / SIZING

Up to 5 gpm (19 Lpm) flow rate

CB20-124E Water Filter Housing

SPECIFICATIONS

Overall Dimensions:

25.875"H x 7.25"W x 8.5"D

Inlet connection:

3/4" FNPT

Outlet connection:

3/4" FNPT

Service Flow Rate:

Maximum 5.0 gpm (19 Lpm)

Pressure Requirements:

20 – 100 psi (1.4 – 6.9 bar), non-shock


Temperature:

35 – 100°F (2 – 38°C)

No electrical connection required

Shipping Weight: 12 lbs.

The contaminants or other substances removed or reduced by this drinking water system are not necessarily in your water. Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.



WARRANTY

Everpure water treatment systems (excluding replaceable elements) are covered by a limited warranty against defects in material and workmanship for a period of five years after date of purchase. Everpure replaceable elements (filter cartridges and water treatment cartridges) are covered by a limited warranty against defects in material and workmanship for a period of one year after date of purchase. See printed warranty for details. Everpure will provide a copy of the warranty upon request.

EVERPURE®

EVERPURE, LLC
1040 Muirfield Drive
Hanover Park, Illinois 60133
Toll Free (800) 323-7873
Tel (630) 307-3000
Fax (630) 307-3030
<http://www.everpure.com>

In Europe:
N.V. EVERPURE (EUROPE) S.A.
INDUSTRIEPARK WOLFSTEE
TOEKOMSTLAAN 30
B-2200 HERENTALS
BELGIUM
TEL 32 -14-283500
FAX 32-14-283505

In Japan:
EVERPURE JAPAN LLC
HASHIMOTO MN BLDG. 7F
3-25-1 HASHIMOTO SAGAMIHARA-SHI
KANAGAWA 229-1103
JAPAN
TEL 81-(0)42-775-3011
FAX 81-(0)42-775-3015