

Project:		AIA#
Item #:	Qty:	SIS#
Model #:		

Beer Line Chillers

1/3 HP Beer Line Chiller

Model: BLC-1/3-E



BLC-1/3-E

STANDARD FEATURES:

- Glycol connections with flared fittings for easy service access
- Durable black vinyl-clad exterior with 16 gauge galvanized steel base
- Stainless steel, CFC-free, foamed-in-place insulated glycol
- High efficiency heat exchanger minimizes glycol bath size to one gallon
- Front located glycol filling port

Certified to CSA STD C22.2 No. 120

Conforms to ANSI/UL STD 471

1/3, 1/2, and 3/4 HP Beer Line Chillers with Remote Installable Control Panel

Models: BLC-1/3, BLC-1/3-2, BLC-1/2, BLC-1/2-2, BLC-3/4, BLC-3/4-2



Intertek Conforms to ANSI/UL STD 471 Certified to CSA STD C22.2 No. 120





BLC-3/4-2

STANDARD FEATURES:

- Control panel is removable and includes wall bracket for remote installation
- Glycol connections with flared fittings for easy service access
- Durable black vinyl-clad exterior with 16 gauge galvanized steel base
- Stainless steel, CFC-free, foamed-in-place insulated glycol
- High efficiency heat exchanger minimizes glycol bath size to one gallon
- Front located glycol filling port
- Digital temperature control with LCD display
- Over-sized condenser coil for maximum efficiency
- Clear glycol bath cover for easy visual inspection
- Available with two recirculating pumps (designated by "-2" suffix in model number)

Intertek
Conforms to ANSI/UL STD 471
Certified to CSA STD
C22.2 No. 120

Glastender, Inc. • 5400 North Michigan Road • Saginaw, MI • 4	8604-9780
989.752.4275 • 800.748.0423 • Fax 989.752.4444	
www.glastender.com	

Specifications subject to change without notice. For current specifications please visit our website.

Approval/Notes:

Printed in USA Rev. 04-11-13 5.01

Remote Draft Beer Line Chillers

Dimensional and Specification Information

Model No.		BLC-1/3-E	BLC-1/3	BLC-1/3-2	BLC-1/2	BLC-1/2-2	BLC-3/4	BLC-3/4-2		
Dimensions†	Length	27"	27"	27"	27"	27"	27"	27"		
	Width	21-1/4"	25-5/8"	25-5/8"	25-5/8"	25-5/8"	25-5/8"	25-5/8"		
	Height	14-3/4"	16"	16"	16"	16"	16"	16"		
		† Note: A minimum six inch clearance should be allowed around the entire unit for proper air flow. Additional clearance should be considered above and in front of the unit for service access.								
Electrical	Voltage	120V	120V	120V	120V	120V	230V	230V		
	Frequency	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz		
	Phase	1ø	1ø	1ø	1ø	1ø	1ø	1ø		
	FLA	13	13	18.6	13.5	19.5	10.1	12.9		
	Dedicated Circuit	20A	20A	30A	20A	30A	20A	20A		
	Electrical Connection	Cord & Plug	Cord & Plug	Hard Wire	Cord & Plug	Hard Wire	Cord & Plug	Cord & Plug		
Refrigerant		R134a	R134a	R134a	R134a	R134a	R134A	R134A		
Compressor		1/3 HP	1/3 HP	1/3 HP	1/2 HP	1/2 HP	3/4 HP	3/4 HP		
Capacities*		2,175 BTU/hr	2,175 BTU/hr	2,175 BTU/hr	3,300 BTU/hr	3,300 BTU/hr	6,375 BTU/hr	6,375 BTU/hr		
		* Note: Rated capacities assume maximum operating ambient temperature of 80°F.								
Max Distance to Taps		125 ft.	125 ft.	125 ft.	250 ft.	250 ft.	400 ft.	400 ft.		
Circulating Pumps		60 gph	60 gph	60 gph	60 gph	60 gph	60 gph	60 gph		
Glycol Bath Capacity		.94 gal	.94 gal	.94 gal	.94 gal	.94 gal	.94 gal	.94 gal.		
Shipping Weight LBS (kg)		128 (58.1)	150 (68.0)	163 (73.9)	153 (69.4)	166 (75.3)	175 (79.5)	193 (87.7)		

Remote Mounted Control Panel Installation Details

The Glastender exclusive, patented beer line chiller design houses the heat exchanger inside the condensing unit compartment. This unique feature allows the control panel with glycol bath and recirculating pump(s) to be easily installed separate from the condensing unit in a more conveniently accessible location. Simply remove the control panel from the condensing unit cabinet and mount it in the desired location. Only glycol and electrical lines need to be run between the control panel and the condensing unit cabinet.

Electrical connection between condensing unit and control panel by local electrician


Glycol line from heat exchanger to bath

Digital temperature control with LCD display

with LCD display

Photo shows BLC-1/3 in an installation setting with the control panel installed remotely from the condensing unit cabinet.





Condensing unit and heat exchanger cabinet

Glycol return from beer tower to heat exchanger

Glycol line from pump to beer tower

Glycol line from bath to pump

Recirculating pump

.94 gallon glycol

Power cord for unit