




portable.
stackable.
storable.

MAXX Edge™ Laminate Buffet Table

SPECIFICATION



30x72", 30x96" with optional 12" wide riser shelf and/or storage rack

Table Tops

- Table core is constructed of 18MM calibrated exterior glue plywood with "bb" face and "cc" back. Meets California Air Resources Board's Phase 2 Formaldehyde Emissions Standards.
- Laminate surface is a WilsonArt® high-pressure laminate
 - Meets or exceeds NEMA specifications
 - GREENGUARD® Indoor Air Quality Certified
 - Wood fiber content constructed of a minimum 20% post-consumer waste paper (SCS certified)
- Backer sheet is phenolic material, color black
 - Constructed of a minimum 30% recycled pre and post-consumer mix (SCS certified)

Utility Table Top

- Steel table runners
 - Consisting of two each 1 3/4" x 1" rails
 - Constructed of 14 gauge, rolled, high carbon steel, running the length of the table
- Support rails are attached to tops with screws

Utility Table Molded Edge

- Table features a poured urethane elastomer edge system designed for specialty molding applications
- Edge has a 3/8" radius, half round shape
- Edge color is black
- Edge is mechanically bonded to the table top and flush with the top and bottom surfaces (no gaps)
- Edge is seamless
- Edge has good color stability and mar resistance, with a tensile strength (ASTM D412) of 1,480 psi and durometer of 95 Shore A

Riser Shelf

- Dimensions
 - 12" wide x 15" tall
 - Length equal to main table length
- Steel table runners
 - Consisting of two each 1 3/4" x 1" rails
 - Constructed of 14 gauge, cold rolled, high carbon steel, running the length of the table
- Support rails are attached to tops with screws

Riser Shelf Molded Edge

- Edges are protected with 0.755" PVC vinyl "T" molding, color black, extruded in a "bull-nose" shape
- Edge molding is secured through serrations in the vinyl molding's "T" base and stapled on both sides of the single molding seam

Legs

- Table legs are constructed of cold-rolled 16 gauge, 1" diameter galvanized steel tubing
- Table legs are 24" wide "H" style
- Locking mechanism is "boss & mate", featuring a détente lock in both the open and closed positions
 - "Gravity-Lock" drop rings also lock legs in open position
- Each legs is attached to table top with twelve (12) countersunk screws
- Table legs fold but do not allow the tables to stack
- Standard table height is 30" from floor to top of table surface

Casters


- Table legs are fitted with four (4) 5" diameter x 1" wide nylon locking casters
- Casters are constructed of steel with a 1/2" thick rubber surface
- Each caster has a load rating of 200 lbs.



portable.
stackable.
storable.

MAXX Edge™ Laminate Buffet Table

SPECIFICATION



Storage Rack

- Storage rack is constructed of ¼" welded steel wire
 - 3" x 3" openings between wires
- Rack is removable
 - Three (3) wire hooks drop over the lower cross bar on each folding leg
- Rack Dimensions
 - 20" inside width (to hold 19 ¾" x 19 ¾" plastic glass racks)
 - 72" table's rack is 60" long
 - 96" table's rack is 84" long
 - 2" deep
- Relative Dimensions
 - 22" from the inside of the bottom of the rack to the bottom of the table
 - 4" ½" from the floor to the bottom of the rack
- 300 lbs distributed load capacity

Metal Finish

- All metal parts are treated for corrosion resistance and paint adhesion
- Powder coated metal surfaces are finished with a baked on black epoxy powder coating for superior resistance to abrasion, marring & scratching

Warranty

PS Furniture warrants that its MAXX Edge Laminate Buffet Tables shall be free from defects in original materials and workmanship for a period of five years from the original shipment date. Warranty on sales for rental use is limited to one year. This warranty shall not apply to normal wear and tear or in the event products are damaged as a result of misuse, abuse, vandalism, neglect, accident, improper application and modification or repair by persons not authorized by PS Furniture. The company will, at its discretion, repair or replace any defects. Any repair or replacement must be approved in advance by the factory before any action is taken. There are no implied warranties of fitness or merchantability, and there are no other express warranties beyond the warranties expressed here.